


# INSTRUCTION MANUAL



## Edu DL Round

<p>1.</p> <p>OFF</p>	<p>2.</p> <p>ø74mm</p>	<p>3.</p>
<p>4.</p> <p>INPUT: AC220~240V</p>	<p>5.</p> <p>FREE SPACE ±11cm</p>	<p>6.</p> <p>Warning: When replacing a halogen lamp, wait for it to cool, for a minimum of 5 minutes</p>
<p>7.</p> <p>ON</p>	<p>Overall Sizes:</p> <p>100mm</p> <p>28mm</p> <p>ø82mm</p> <p>30°</p>	