

INSTRUCTION MANUAL



Qure DL GU10-1
44749 / 90849

<p>1.</p>	<p>2.</p>	
<p>3.</p> <p>INPUT: AC220-240V</p>	<p>4.</p> <p>FREE SPACE</p> <p>≥10CM</p>	<p>5.</p> <p>① ↑</p> <p>② ↑</p> <p>warning: when replacing a halogen lamp, wait for it to cool, for a minimum of 5 minutes</p>
<p>6.</p>	<p>Overall Sizes:</p>	